

## 0273 系列



型号	P0273-EO01																																																																																
订货号	4042.0273.1501																																																																																
起订量	-	1																																																																															
适用激光	-	工业: Ti:Sa, Diode, Nd:YAG, harmonic Nd:YAG (2x; 3x; 4x), CO <sub>2</sub> 医疗: UV, KTP, Diode(红), Diode, Alexandrite, Nd:YAG, CO <sub>2</sub>																																																																															
材料	-	特殊塑料																																																																															
颜色	-	棕色																																																																															
防护等级	-	<table border="0"> <tr> <td>180 – 315</td> <td>D LB10+IR LB5+M LB6Y</td> <td>(OD 10+)</td> <td>723 – 729</td> <td>D LB6+IR LB7+M LB7Y</td> <td>(OD 7+)</td> </tr> <tr> <td>&gt; 315 – 532</td> <td>D LB6+IR LB8+M LB7Y</td> <td>(OD 8+)</td> <td>730 – 780</td> <td>D LB6+IR LB8+M LB7Y</td> <td>(OD 8+)</td> </tr> <tr> <td>533 – 538</td> <td>DIRM LB5</td> <td>(OD 5+)</td> <td>781 – 815</td> <td>D LB6+IRM LB7</td> <td>(OD 7+)</td> </tr> <tr> <td>539 – 542</td> <td>DIRM LB4</td> <td>(OD 4+)</td> <td>816 – 839</td> <td>D LB6+IRM LB8</td> <td>(OD 8+)</td> </tr> <tr> <td>543 – 545</td> <td>DIRM LB3</td> <td>(OD 3+)</td> <td>840 – 1080</td> <td>D LB6+IRM LB8</td> <td>(OD 8+)</td> </tr> <tr> <td>546 – 550</td> <td>DIRM LB2</td> <td>(OD 2+)</td> <td>950 – 1065</td> <td>D LB6+IRM LB9</td> <td>(OD 9+)</td> </tr> <tr> <td>551 – 558</td> <td>DIRM LB1</td> <td>(OD 1+)</td> <td>1081 – 1087</td> <td>DIRM LB6</td> <td>(OD 6+)</td> </tr> <tr> <td>622 – 648</td> <td>DIRM LB1</td> <td>(OD 1+)</td> <td>1088 – 1098</td> <td>DIRM LB5</td> <td>(OD 5+)</td> </tr> <tr> <td>649 – 660</td> <td>DIRM LB2</td> <td>(OD 2+)</td> <td>1099 – 1109</td> <td>DIRM LB4</td> <td>(OD 4+)</td> </tr> <tr> <td>661 – 696</td> <td>DIRM LB3</td> <td>(OD 3+)</td> <td>1110 – 1123</td> <td>DIRM LB3</td> <td>(OD 3+)</td> </tr> <tr> <td>697 – 708</td> <td>DIRM LB4</td> <td>(OD 4+)</td> <td>1124 – 1141</td> <td>DIRM LB2</td> <td>(OD 2+)</td> </tr> <tr> <td>709 – 716</td> <td>DIRM LB5</td> <td>(OD 5+)</td> <td>1142 – 1170</td> <td>DIRM LB1</td> <td>(OD 1+)</td> </tr> <tr> <td>717 – 722</td> <td>DIRM LB6</td> <td>(OD 6+)</td> <td>4780 – 11500</td> <td>DI LB4 + R LB3Y</td> <td>(OD 4+)</td> </tr> </table>		180 – 315	D LB10+IR LB5+M LB6Y	(OD 10+)	723 – 729	D LB6+IR LB7+M LB7Y	(OD 7+)	> 315 – 532	D LB6+IR LB8+M LB7Y	(OD 8+)	730 – 780	D LB6+IR LB8+M LB7Y	(OD 8+)	533 – 538	DIRM LB5	(OD 5+)	781 – 815	D LB6+IRM LB7	(OD 7+)	539 – 542	DIRM LB4	(OD 4+)	816 – 839	D LB6+IRM LB8	(OD 8+)	543 – 545	DIRM LB3	(OD 3+)	840 – 1080	D LB6+IRM LB8	(OD 8+)	546 – 550	DIRM LB2	(OD 2+)	950 – 1065	D LB6+IRM LB9	(OD 9+)	551 – 558	DIRM LB1	(OD 1+)	1081 – 1087	DIRM LB6	(OD 6+)	622 – 648	DIRM LB1	(OD 1+)	1088 – 1098	DIRM LB5	(OD 5+)	649 – 660	DIRM LB2	(OD 2+)	1099 – 1109	DIRM LB4	(OD 4+)	661 – 696	DIRM LB3	(OD 3+)	1110 – 1123	DIRM LB3	(OD 3+)	697 – 708	DIRM LB4	(OD 4+)	1124 – 1141	DIRM LB2	(OD 2+)	709 – 716	DIRM LB5	(OD 5+)	1142 – 1170	DIRM LB1	(OD 1+)	717 – 722	DIRM LB6	(OD 6+)	4780 – 11500	DI LB4 + R LB3Y	(OD 4+)
180 – 315	D LB10+IR LB5+M LB6Y	(OD 10+)	723 – 729	D LB6+IR LB7+M LB7Y	(OD 7+)																																																																												
> 315 – 532	D LB6+IR LB8+M LB7Y	(OD 8+)	730 – 780	D LB6+IR LB8+M LB7Y	(OD 8+)																																																																												
533 – 538	DIRM LB5	(OD 5+)	781 – 815	D LB6+IRM LB7	(OD 7+)																																																																												
539 – 542	DIRM LB4	(OD 4+)	816 – 839	D LB6+IRM LB8	(OD 8+)																																																																												
543 – 545	DIRM LB3	(OD 3+)	840 – 1080	D LB6+IRM LB8	(OD 8+)																																																																												
546 – 550	DIRM LB2	(OD 2+)	950 – 1065	D LB6+IRM LB9	(OD 9+)																																																																												
551 – 558	DIRM LB1	(OD 1+)	1081 – 1087	DIRM LB6	(OD 6+)																																																																												
622 – 648	DIRM LB1	(OD 1+)	1088 – 1098	DIRM LB5	(OD 5+)																																																																												
649 – 660	DIRM LB2	(OD 2+)	1099 – 1109	DIRM LB4	(OD 4+)																																																																												
661 – 696	DIRM LB3	(OD 3+)	1110 – 1123	DIRM LB3	(OD 3+)																																																																												
697 – 708	DIRM LB4	(OD 4+)	1124 – 1141	DIRM LB2	(OD 2+)																																																																												
709 – 716	DIRM LB5	(OD 5+)	1142 – 1170	DIRM LB1	(OD 1+)																																																																												
717 – 722	DIRM LB6	(OD 6+)	4780 – 11500	DI LB4 + R LB3Y	(OD 4+)																																																																												
VLT(约)	%	15																																																																															
镜片厚度(约)	mm	2.0																																																																															
镜框类型	-	ONTOR																																																																															
镜框材料	-	塑料																																																																															
镜框颜色	-	黑 / 灰																																																																															
重量(约)	g	10																																																																															
推荐男 / 女	-	男 / 女																																																																															
适合佩戴 矫正眼镜	-	是																																																																															
安全认证	-	EN 207, PF CE																																																																															
可选配件	-	微型 LED 电筒 <a href="#">4500.2000.2003</a>																																																																															